

Samples can deviate in the execution from the serie.

- Dimensions and tolerances can be specified only after the testing of the devices for the mass production definitely





Tab material: Isotan (54%Cu,44%Ni,Mn)

All framed values will be used for dimension checking

The Products of Renata SA are neither designed nor authorized for use in certain areas of appliction of environment. For further details we refer to our webpage: www.renata.com/downloads/restriction of use

Rev.	① 12.09.2019 SRi Rev. ⊙					Customer's Approval					
Rev.	0		•	Rev.	0		•		Date		
Rev.	0		•	Rev.	0		•	7 +	Signature		
Titel:								Scale	Drawn	05.11.07	SRi
CR2477NSM								2:1	Checked	13.09.19	HSn
									Approved	16.09.19	MDi
1		ata 🔊		СН		.52 Itir itzerland	•	3.9207.4-1			